

Fleet Name

Vehicle Mileage

Truck Unit #

Email Address

VIN #

(required field)

Phone Number

Max Engine RPM

(required field)

R.O. Number

Top Gear Ratio
of Transmission

(required field)

Case Number

Menu

Work Sheet

Side View

Directions

Reference

Next

Exit Tool

Print

Email

Save As

Calculate

Reset

Comments



Side Angle 1

+ -

Side Angle 2

+ -

Side Angle 3

+ -

Side	<input type="text"/>	<input type="text"/>
U-Joint Angle	#1	#2
Compound	<input type="text"/>	<input type="text"/>

Menu

Work Sheet

Top View

Directions

Reference

Next

Exit Tool

Print

Email

Save As

Calculate

Reset

RESULTS Side Angle 2

ACC Shaft

ACC Drive


ACC Coast

Max Engine RPM in
Top Gear

Top Gear Ratio of
Transmission

Max Driveline
Speed RPM

Max Driveline
Speed Rad / Sec



Menu

Work Sheet

Side View

Directions

Reference

Next

Exit Tool

Print

Email

Save As

Calculate

Reset

RESULTS Top Angle 2

ACC Shaft

ACC Drive

ACC Coast

Max Engine RPM in
Top Gear

Top Gear Ratio of
Transmission

Max Driveline
Speed RPM

Max Driveline
Speed Rad / Sec