

Fleet Name

Vehicle Mileage

Truck Unit #

Email Address

VIN #

(required field)

Phone Number

Max Engine RPM

(required field)

R.O. Number

Top Gear Ratio  
of Transmission

(required field)

Case Number

Top Gear Ratio  
of Auxiliary

(required field)

Menu

Work Sheet

Side View

Directions

Reference

Next

Exit Tool

Print


Email

Save As

Calculate

Reset

Comments



| Side          |    |    |    |    |    |  |  |    |  |    |
|---------------|----|----|----|----|----|--|--|----|--|----|
| U-Joint Angle | #1 | #2 | #3 | #4 | #5 |  |  | #6 |  | #7 |
| Compound      |    |    |    |    |    |  |  |    |  |    |

Menu

Work Sheet

Top View

Directions

Reference

Next

Exit Tool

Print

Email

Save As

Calculate

Reset

### PHASE

Drive (inertial) rad/sec^2 

Coast (inertial) rad/sec^2 

Shaft Acceleration rad/sec^2 

Shaft Residual Angle 

Lowest Residual Angle 

RESULTS Side Angle 2 Side Angle 7


ACC Shaft  

ACC Drive  

ACC Coast  

Max Engine RPM  
in Top Gear 

|                                  | Transmission         | Auxiliary            | Transmission<br>x Auxiliary |
|----------------------------------|----------------------|----------------------|-----------------------------|
| Top Gear Ratios                  | <input type="text"/> | <input type="text"/> | <input type="text"/>        |
| Max Driveline<br>Speed RPM       | <input type="text"/> | <input type="text"/> | <input type="text"/>        |
| Max Driveline<br>Speed Rad / Sec | <input type="text"/> | <input type="text"/> | <input type="text"/>        |

|               |    |    |    |    |    |    |    |  |  |  |
|---------------|----|----|----|----|----|----|----|--|--|--|
| Top           |    |    |    |    |    |    |    |  |  |  |
| U-Joint Angle | #1 | #2 | #3 | #4 | #5 | #6 | #7 |  |  |  |
| Compound      |    |    |    |    |    |    |    |  |  |  |

[Menu](#)
[Work Sheet](#)
[Side View](#)
[Directions](#)
[Reference](#)
[Next](#)
[Exit Tool](#)
[Print](#)
[Email](#)
[Save As](#)
[Calculate](#)
[Reset](#)

### PHASE

Drive (inertial) rad/sec^2   
 Coast (inertial) rad/sec^2   
 Shaft Acceleration rad/sec^2   
 Shaft Residual Angle   
 Lowest Residual Angle

| RESULTS   | Top Angle 2          | Top Angle 7          |
|-----------|----------------------|----------------------|
| ACC Shaft | <input type="text"/> | <input type="text"/> |
| ACC Drive | <input type="text"/> | <input type="text"/> |
| ACC Coast | <input type="text"/> | <input type="text"/> |

Max Engine RPM  
 in Top Gear

|                                  | Transmission         | Auxiliary            | Transmission<br>x Auxiliary |
|----------------------------------|----------------------|----------------------|-----------------------------|
| Top Gear Ratios                  | <input type="text"/> | <input type="text"/> | <input type="text"/>        |
| Max Driveline<br>Speed RPM       | <input type="text"/> | <input type="text"/> | <input type="text"/>        |
| Max Driveline<br>Speed Rad / Sec | <input type="text"/> | <input type="text"/> | <input type="text"/>        |