

Fleet Name

Vehicle Mileage

Truck Unit #

Email Address

VIN #

(required field)

Phone Number

Max Engine RPM

(required field)

R.O. Number

Top Gear Ratio
of Transmission

(required field)

Case Number

Menu

Work Sheet

Side View

Directions

Reference

Next

Exit Tool

Print


Email

Save As

Calculate

Reset

Comments



Side								
U-Joint Angle	#1		#2		#3		#4	#5
Compound								

Menu

Work Sheet

Top View

Directions

Reference

Next

Exit Tool

Print

Email

Save As

Calculate

Reset


RESULTS	Side Angle 2	Side Angle 3	Side Angle 4	Side Angle 5
ACC Shaft				
ACC Drive				
ACC Coast				

Max Engine RPM in Top Gear

Top Gear Ratio of Transmission

Max Driveline Speed RPM

Max Driveline Speed Rad / Sec



[Menu](#)
[Work Sheet](#)
[Side View](#)
[Directions](#)
[Reference](#)
[Next](#)
[Exit Tool](#)
[Print](#)
[Email](#)
[Save As](#)
[Calculate](#)
[Reset](#)

RESULTS	Top Angle 2	Top Angle 3	Top Angle 4	Top Angle 5
ACC Shaft	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
ACC Drive	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
ACC Coast	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>

Max Engine RPM in Top Gear	<input type="text"/>
Top Gear Ratio of Transmission	<input type="text"/>

Max Driveline Speed RPM	<input type="text"/>
Max Driveline Speed Rad / Sec	<input type="text"/>